



Penetrant Testing

Product information
MR[®] Piccolo Pen




MR[®] Piccolo-Pen

MR[®] Chemie GmbH has developed a novelty regarding application methods for penetrant products: MR[®] Piccolo-Pen offers an alternative to the standard application methods like spraying or brushing.

This „fast pen for tiny surface discontinuities“ is intended for a quick and specific use and has proven its worth in practice.

MR[®] Piccolo-Pen is especially useful in areas where you know discontinuities occur by experience. The pen is mainly used by automobile or aircraft industry as well as service industries (TÜV, etc.).



The complete penetrant system is available:

Penetrant fluorescent, Penetrant red + fluorescent, remover and developer

1 Set contains:

- | | | |
|-------|-----------------------|--|
| 1 pen | MR [®] 670 F | Penetrant fluorescent
(free of mineral oil, water and solvent removable) |
| 1 pen | MR [®] 68 C | Penetrant red and fluorescent
(without AZO-dye, approved acc. to EN ISO 3452-2) |
| 1 pen | MR [®] 88 | Remover
(approved acc. to EN ISO 3452-2) |
| 1 pen | MR [®] 70 | Developer
(solvent based, approved acc. to EN ISO 3452-2) |

Of course you may purchase single pens or arrange the set of 4 according to your wishes.

